




Sezione A-A  
(Section)



Note: (Notes)

- 1 Noryl (UL 94-V0) Colore Nero (Black colour).
- 2 Tolleranza non Cumulativa.  
(Non-Cumulative Tolerance).
- 3 OBSOLETE

| N° Pos. | Part Number | Dim. "A" | Dim. "B" | Mat. |
|---------|-------------|----------|----------|------|
| 22      | 280642      | 53,34    | 58,2     | 1    |
| 15      | 280641      | 35,56    | 40,4     | 1    |
| 12      | 280640      | 27,94    | 32,8     | 1    |
| 9       | 280639      | 20,32    | 25,1     | 1    |
| 8       | 280638      | 17,78    | 22,6     | 1    |
| 4       | 280637      | 7,62     | 12,5     | 1    |

|           |                                     |      |           |
|-----------|-------------------------------------|------|-----------|
| J         | OBSOLETE P/N 280639<br>ETOP-0258-92 | F.B. | 18 JUL 92 |
| D         | 280641.0: OBSOLETE                  | EB   | 10-7-92   |
| C         | Revised note                        | EB   | 29-9-86   |
| B         | Revised and Redrawn                 | EB   | 29-9-86   |
| REV.      | REVISION                            | DIS. | DATA      |
| REV. LTR. | (REVISION RECORD)                   | (DR) | (DATE)    |

|                                                                                                                                                                  |  |                                                                     |  |                                       |  |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|---------------------------------------------------------------------|--|---------------------------------------|--|
| FINITURA / COLORE<br>(FINISH / COLOUR)                                                                                                                           |  | MATERIALE<br>(MATERIAL)                                             |  | NUMERO<br>(PART NUMBER)               |  |
| CUSTOMER DWG.<br>FOR REFERENCE ONLY                                                                                                                              |  | DISEGNO PER CLIENTE<br>SOLO PER RIFERIMENTO                         |  |                                       |  |
| THIS DRAWING IS UNPUBLISHED                                                                                                                                      |  | RELEASE FOR PUBLICATION                                             |  |                                       |  |
| © COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA ALL INTERNATIONAL RIGHT RESERVED AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING |  |                                                                     |  |                                       |  |
| TOLLERANZE: SE NON DIVERSAMENTE SPECIFICATO<br>(TOLERANCES UNLESS OTHERWISE SPECIFIED)                                                                           |  | DIAM. ISOLANTE<br>(INS. DIA. RANGE)                                 |  | RANGO FILO<br>(WIRE RANGE)            |  |
| ± 0,3                                                                                                                                                            |  |                                                                     |  | SCALA<br>(SCALE)<br>5:1               |  |
| ANGOLI<br>(ANGLES) ± 2°                                                                                                                                          |  | AMP AMP ITALIA S.p.A.<br>Corso F.lli Cervi, 15<br>COLLEGNO (TORINO) |  |                                       |  |
| DIS.<br>(DR)                                                                                                                                                     |  | DESCRIZIONE<br>(DESCRIPTION)                                        |  |                                       |  |
| Bassano 29-9-86                                                                                                                                                  |  | AMP MODU II Pin Housing,<br>Double Row, Crimped Snap-In.            |  |                                       |  |
| CONT.<br>(CHK)                                                                                                                                                   |  | LOC. SIZE                                                           |  | NUMERO<br>(DWG NO)                    |  |
| APP.<br>(APP)                                                                                                                                                    |  | I A3 C                                                              |  | 280637                                |  |
|                                                                                                                                                                  |  |                                                                     |  | REV. FOGLIO<br>(SHEET)<br>DI 1 (OF 1) |  |
|                                                                                                                                                                  |  |                                                                     |  | 8                                     |  |