

PC-CONTACT ELECTRONIC SERVICE CASE

The clearly arranged tool case for the prompt and efficient servicing of computers

6100 **BERNSTEIN** PC-CONTACT with tool set

6115 **BERNSTEIN** PC-CONTACT without tool set

Description:

Elegant, hard-wearing case made from deep-drawn, impact-resistant, grained dark brown plastic with a continuous bronze anodised aluminium frame, dustproof and rainproof, acid-resistant, scratch-resistant and non-slip.

65 tools are clearly arranged in pockets on one swiveling and one removable tray. The back of the panel has elastic loops to take documents, pcb's, cd's, etc. The lid of the case is padded with foam rubber. The split plastic tray in the bottom of the case, which is intended to take spare parts, measuring instruments and soldering equipment, is 60 mm high.

The case has a lock strip with 2 locks and is centrally lockable. It has loops at the sides for attaching a carrying strap.

Outside dimensions: 460 x 350 x 170 mm

Weight without tools: approx. 3.700 kg

Weight with tools: approx. 5.400 kg

Tool set:

No.	Description of individual tools	No.	Description of individual tools
2-127	Tin knife , with plastic handle, 115 mm	4-272	Cross-recess screwdriver , Supadriv/Pozidriv as above, size 1
2-132	Spring hook , nickel-plated and insulated, 175 mm	4-281	Electronics cross-recess screwdriver with special black handle and swivel top, size 000, blade chrome vanadium, chrome-plated, with black tip
2-161	Magnetic bar with double ball- and socket joint, slewable, 215 mm	4-282	Electronics cross-recess screwdriver as above, size 00
2-166	Contact cleaner , made from glass fibre, 115 mm	4-283	Electronics cross-recess screwdriver as above, size 0
2-265	2 Test prods , red and black, extremely slim, pointed and flexible, blade made from 1 mm steel wire, 155 mm	4-284	Electronics cross-recess screwdriver as above, size 1
2-275	Repair mirror , 21 mm Ø, with handle, 180 mm long	4-331	Assembly screwdriver with plastic handle, nickel-plated blade, 45 x 6 mm, with special square pattern BERNSTEIN handle
2-601	IC tweezers , nickel-plated, 125 mm, for gripping, inserting and removing IC's	4-343 VDE	Voltage tester , blade 60 x 3 mm
2-620	PLCC extractor for easy removal of plug-in PLCC's	4-407	Retaining screwdriver , 110 x 4 mm
3-901-12	Side cutters , 120 mm, for hard wire up to 0.4 mm, for soft wire up to 1.0 mm, burnished, with orange insulation	5-107	Engineer's tweezers , made from steel, with bent tips, 150 mm
3-906-12	End cutters , 120 mm, for soft wire up to 0.8 mm, burnished, with orange insulation	5-117	Engineer's tweezers , straight-flat-wide, 145 mm, nickel-plated
3-932-12	Flat nose pliers , 120 mm, burnished, with orange insulation	5-210	Needle files , 6-piece set
3-933-12	Snipe nose pliers , 120 mm, burnished, with orange insulation	5-305	Combination scissors , stainless, serrated, compression spring, plastic handles, 140 mm
3-945-12	Snipe nose pliers , 145 mm, angular long jaws, burnished with orange insulation	6-200	Socket spanner set , 8 pieces, in plastic case, 1 plastic handle, 7 socket spanners 4.0, 5.5, 6.0, 7.0, 8.0, 9.0 and 10.0 mm
4-141	Screwdriver , with special square pattern BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, with black tip, 75 x 3.5 mm	6-750	Special open-end wrenches , 6-piece set, nickel-plated, 3 x 3.5, 4 x 4.5, 5 x 5.5, 6 x 6.5, 7 x 8, 9 x 10 mm, material thickness 1.5 resp. 2.0 mm
4-142	Screwdriver as above, blade 100 x 4 mm	6-771	Adjustable wrench , jaw opening 0 - 12 mm, total length 100 mm
4-161	Electronics screwdriver with special handle and swivel top, blade chrome vanadium, chrome-plated, with black tip, blade 40 x 1.0 mm	6-880	Set of wrench keys , 8 pieces in plastic case, 1/16", 5/64", 3/32", 1/8", 5/32", 3/16", 7/32", 1/4"
4-162	Electronics screwdriver as above, blade 40 x 1.5 mm	6-964 L	TORX screwdriver with special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, black tip, size T 9 with hole
4-163	Electronics screwdriver as above, blade 40 x 2.0 mm	6-965 L	TORX screwdriver as above, size T 10 with hole
4-165	Electronics screwdriver as above, blade 50 x 3.0 mm	6-966 L	TORX screwdriver as above, size T 15 with hole
4-271	Cross-recess screwdriver , Supadriv/Pozidriv, Size 0, with special square pattern BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, with black tip	7-425	Dust brush

To complete the set we recommend:

- 8-135 **ERSA "Multitip" soldering iron**, 15 W, 220 V
- 8-390 **Desoldering pump**, length 195 mm, 20 mm Ø
- 9-325 **Plastic box**, with hinged lid and adjustable compartments, 200 x 130 x 30 mm

PC-CONTACT 6100 ELECTRONIC SERVICE CASE

Elegant, modern tool case for the most exacting standards



The service case

for the computer technology
with the current tool assortment