


**HC-B 6-TFL-43/O1M20S**

Order No.: 1604732



HEAVYCON sleeve housing B6, for single locking latch, height 43 mm,  
with support 1xM20, lateral conductor exit

**Commercial data**

|                          |   |
|--------------------------|---|
| GTIN (EAN)               | <br>4 017918 881030 |
| sales group              | D002  |
| Pack                     | 10 pcs.   |
| Customs tariff           | 85389099  |
| Catalog page information | Page 570 (PC-2011)  |

**Product notes**

WEEE/RoHS-compliant since:  
01/31/2006



[http://  
www.download.phoenixcontact.com](http://www.download.phoenixcontact.com)  
Please note that the data given  
here has been taken from the  
online catalog. For comprehensive  
information and data, please refer  
to the user documentation. The  
General Terms and Conditions of  
Use apply to Internet downloads.

**Technical data****General data**

|        |  |
|--------|--|
| Note   | For contact inserts HC-B6, BB10, DD24, M |
| Design | B6                                       |
| Height | 44 mm                                    |
| Width  | 43 mm                                    |
| Length | 60 mm                                    |

|                                  |                          |
|----------------------------------|--------------------------|
| Housing type                     | Sleeve housings          |
| Locking type                     | for single locking latch |
| No. of cable exits               | 1                        |
| Cable exit                       | Lateral                  |
| Pg screw connection              | None                     |
| Type of the screw connection     | 1x M20                   |
| Degree of protection for housing | IP65                     |
| Ambient temperature (operation)  | -40 °C ... 125 °C        |
| Housing material                 | Aluminum, die-cast       |
| Housing surface material         | Powder-coated, gray      |

### Certificates / Approvals



Certification

GOST

### Diagrams/Drawings

Dimensioned drawing

