



ENGLISH

Datasheet

## RS Pro Steel Abrasive End Brush, 12000rpm, 25mm Diameter

RS Stock No: **374-503**



### Product Details

RS Pro abrasive end brush with steel bristle, has a diameter of 25 mm and shaft diameter of 6 mm. It is perfect for cleaning or deburring hard to reach areas and is available in mild steel wire or stainless steel wire. The steel wire version is identified by green mark on cup section.

### Features and Benefits

- Stainless steel bristle construction
- 12000 rpm maximum safe speed
- Shank fixing type
- 35 mm long bristle



ENGLISH

### Specifications:

Bristle Material	Steel
Fixing Type	Shank
Bristle Length	35 mm
Diameter	25 mm
Fixing Size	6 mm
Maximum Safe Speed	12000 rpm