

PC8-10

ABB contact for United
States of America



General Information

Extended Product Type:	PC8-10
Product ID:	1SNA163313R2400
EAN:	3472591633139
Catalog Description:	PC8-10 Lateral Jumper Bars Black
Long Description:	PC8-10 - Lateral Jumper Bars - 10 poles - Black - 8mm Spacing

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Lateral Jumper Bars

Ordering

EAN:	3472591633139
Minimum Order Quantity:	10 piece
Customs Tariff Number:	39269097

Dimensions

Product Net Weight:	14.00 g
----------------------------	---------

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Gross Weight:	0.14000 kg
Package Level 1 EAN:	3472591633139
Package Level 2 Units:	500 piece

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
---------------------------------	--

Technical UL/CSA

Flammability According to UL94:	V0
--	----

Additional Information

Ambient Temperature:	-5 ... +40 °C
Color:	Black
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Function:	Lateral Jumper Bars
IIT Publishing Status:	Level 0 - Information enabled
Insulation Material:	Polyamide
Mounting Type:	1 - Rated voltage: 630 V (IEC) / 150 V (UL) (□) 2 - Rated voltage: 630 V (IEC) / 300 V (UL) (□) a - End section ES10-ST (□) b - End stop BAZ1
Product Main Type:	PC
Product Name:	Jumper Bar
Rated Current (I_n):	Main Circuit 50 A
Rated Voltage (U_r):	630 V
Spacing:	8 mm

Sub-Function 2: Lateral

Certificates and Declarations (Document Number)

Declaration of Conformity - CE: 1SND225001C1009
GOST Certificate: 1SND161005A1104

Classifications

E-nummer: 2925679
ETIM 4.0: EC000489 - Cross-connector for terminal block
ETIM 5.0: EC000489 - Cross-connector for terminal block
Object Classification Code: X

