

ACD508ASM - Load Spreading Rivet (LSR)

General Part Information		
Product Description		ACD508ASM
Article Number		80579.00
Rivet Type	i	Load Spreading Rivet (LSR)
Standard Bulk Pack Quantity		5000.00
Application / Features	i	



Geometry / Dimensions / Performance		
Head Style	i	Domed
Body Diameter Ø (mm)		4.00
Body Length (mm)		17.50
Min. Grip Range (mm)		0.00
Max. Grip Range (mm)		6.35
Min. Hole Diameter (mm)		4.20
Max. Hole Diameter (mm)		4.30
Min. Flange Diameter (mm)		7.60
Max. Flange Diameter (mm)		8.25
Flange Thickness (mm)		1.34
Mandrel Diameter (mm)		2.29
Nominal Shear Strength (N)		700.00
Nominal Tensile Strength (N)		900.00

Material / Finish / Weight		
Body Material	i	AlMg3.5
Mandrel Material		Aluminium
Finish		Clean
Weight per thousand (kg)		0.94