



ENGLISH

Datasheet

Stock No: 291-0022

RS Pro ATEX M20 Brass Cable Gland



Product Details

Cable Glands M20

- Brass body
- M20 thread
- To BS6207 pt2
- 10 glands per box

Approvals

Certificate: SIRA 02ATEX1305X

Specifications:

Thread Size	M20
Material	Brass
Maximum Cable Diameter	6.6mm
Minimum Operating Temperature	-20°C
Maximum Operating Temperature	+450°C
Hazardous Area Certification	ATEX