



ENGLISH

Datasheet

Conquer Quick Acting F LBC fuse, 160 mA 5 x 20 mm BP

RS Stock Number: **563-508**

Part Number: **VBS USL 250mA 250V (05)**



Product Details

Conquer quick acting LBC fuse is current rated for 160 mA. This F-speed, glass bodied fuse is ideal for protection of electrical circuits and consumer appliances.

**Specifications:**

Body Material	Glass
Breaking Capacity (at Maximum Voltage Rating)	35 A
Current Rating	0.16 A
Diameter	5.2 mm
Fuse Speed	F
High Rupture Capacity	No
Includes Indicator	No
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-55°C
Operating Temperature Range	-55 to +125°C
Overall Dimensions	5.2 x 20 mm
Overall Length	20 mm
Resistance	2.6655 Ω
Size Designation	Miniature
Voltage Rating	250 V ac
Standards Met	CSA Acceptance, UL Recognised, RoHS Compliant, VDE, BSI, CCC, KTL, SEMKO Approved
UL File Number	E82636