

Etching machines

SPRAY ETCHING



Etching time 2 minutes with new ferric chloride at 30 °C.

2 models: GIROJET1 -
GIROJET2
- useful etching area:
200x300mm
- timer: 0 to 7 min
Both models have built-in heating.

Specially designed for electronics engineering departments and laboratories. This etching machine has the qualities of an industrial machine without either the volume or the installation requirements (water supply, drainage, three-phase supply, etc.). It means circuits can be produced on site and without delay. Built-in drainage. Problem-free installation. Compact, economical and quick, reliable, safe and clean, easy to maintain, heavy-duty.

Girojet 1 - Single-sided

- Dimensions (l x H x P) : 235 x 460 x 500 mm
- Weight : 8 kg environ
- Capacity : 8 litres
- Do not exceed
- the filling level

Item code	DP 8
-----------	------

Girojet 2 - Double-sided

- Dimensions (l x H x P) : 235 x 460 x 500 mm
- Weight : 10 kg environ
- Capacity : 8 litres

Item code	DP 9
-----------	------



Multi-circuit clip
For etching several small circuits at the same time

For Girojet 1 and 2	DP 12
---------------------	-------