



ENGLISH

## RS Pro PUR 10m Long transparent Flexible Ducting Reinforced, 12mm Bend Radius , Applications Various

RS Stock No. 362-2091

Brand RS Pro



Image representative of range

# Product Details

## Flexible Ducting (Zinc plated helix)

An RS Pro polyurethane (PU) hosing with a galvanised steel spiral. Designed to be self-extinguishing and can be used for suction and the transport of dusts, chips and abrasive materials.

Zinc plated spring-steel spiral helix between two layers of crystal clear polyurethane

Highly flexible with excellent internal and external abrasion resistance

May also be used in foundry, general industrial and agricultural applications

Temperature range -40 to +90°C

### Note

All data refers to performance at 18°C. Any changes in temperature will affect the performance data



Polyurethane Ducting - Lightweight

---

# Specifications

Not what you're looking for? Select the attributes you require, then click the button below

<input type="checkbox"/> Inner Diameter	45mm
<input type="checkbox"/> Outer Diameter	50mm
<input type="checkbox"/> Material	PUR
<input type="checkbox"/> Length	10m
<input type="checkbox"/> Suitable Applications	Agriculture, Foundry, Industrial
<input type="checkbox"/> Colour	Transparent
<input type="checkbox"/> Bend Radius	12mm
<input type="checkbox"/> Reinforced	Yes

---