


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
FT	0					
		D		REVISED PER 0G3B-0293-02	5/22/02	SS



NOTES:

- WILL ACCEPT (8) MULTIMATE SOCKETS AND (5) TYPE XII FEMALE CONTACTS.
- MAX WIRE INSULATION DIAMETERS:
MULTIMATE 3.43 [.135] MAX DIA.
TYPE XII 5.59 [.220] MAX DIA.
- CONTACT CAVITIES IDENTIFIED BY CHARACTERS ON FRONT AND REAR FACES OF CONNECTOR.
- THIS PLUG ASSEMBLY MATES WITH RECEPTACLE 211825-1.

- 5 COUPLING RING: POLYESTER, BLACK
- 6 COUPLING RING: NORYL, BLACK

6	211824-2
5	211824-1
PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.FOLTZ	04/04/95	tyco Electronics		Tyco Electronics Corporation Harrisburg, PA 17105	
		CHK R.STONE	04/05/95				
DIMENSIONS: INCHES		APVD A.FRANTUM	04/06/95	NAME			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC				
	0 PLC ± -		-				
	1 PLC ± -		-				
	2 PLC ± 0.13 [.005]		-				
	3 PLC ± -		-				
4 PLC ± -		APPLICATION SPEC					
ANGLES ± -		-					
MATERIAL	FINISH	WEIGHT	-	SIZE A2	CAGE CODE 00779	DRAWING NO C-211824	RESTRICTED TO -
SEE CALLOUT	-	CUSTOMER DRAWING			SCALE 2:1	SHEET 1 of 1	REV D