


Textile EMC gaskets



Part no.: 21101-855

Features:

- Textile EMC gasket is affixed laterally on the front panel or in the groove of the right-hand profile as appropriate.
- Temperature range -40 °C ... +70 °C



Technical information:

Height	Height	Qty/PU
6 U	232 mm	10 piece

Delivery comprises:

Item	Qty	Description
1	100	EMC sealing (textile), core: foam, sleeve: textile cladding with CuNi coating

Note:

- EMC gaskets (textile) are required for shielding the front panels