


Profile gasket - HC-B 10-PR-DI-ADVANCE-STA - 1637223

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Profile gasket for ADVANCE housing HC-B10.....STA of B10 type



Key commercial data

Packing unit	10 pc
Minimum order quantity	50 pc
GTIN	 4 046356 158312
Weight per Piece (excluding packing)	3.13 g
Custom tariff number	40169300
Country of origin	Germany

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

General

Material	NBR
----------	-----

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27449290

Profile gasket - HC-B 10-PR-DI-ADVANCE-STA - 1637223

Classifications

ETIM

ETIM 3.0	EC001181
ETIM 4.0	EC001181
ETIM 5.0	EC001181

UNSPSC

UNSPSC 6.01	30211817
UNSPSC 7.0901	39121416
UNSPSC 11	43172601
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC
