

C15 SOLDERING IRON

- Ergonomic miniature handle
- Iron plated, nickel coated bit for long life
- Upto 20,000 operations tip life
- 11 replacement tips in range
- Choice of Burnproof Silicone cable or standard pvc cable
- Voltages from 12 - 230VAC available



SPECIFICATIONS

Voltage	230, 115, 24, 12
Temperature	370°C
Power	15W
Leakage current	3.5 μ A
Fitted bit	820 (2.3mm)
Cable types	PVC or Silicone
Cable Length	1.5 mtr
Plug	UK, EU, USA
Dims (Tip to handle)	147mm

- Manufactured to Din EN 60335-2-45
- CE & EMC Low Voltage directive conformity
- Thermally balanced



Replacement Bits - MK2 series



Replacement Element



Safety Stand ST6A