

## COMMON FEATURES

- Suitable for bits and accessories with SDS-plus shank end
- With the appropriate accessories, it is also suitable for bits and accessories with cylindrical shank end (no impact)
- Hammer stop
- Rotation stop
- Clockwise and anticlockwise rotation
- Metabo "Quick" chuck change
- Robust Metabo Marathon motor
- Pneumatic high-performance hammer mechanism
- Die cast aluminium gear housing
- Ergonomic housing design for fatigue-proof operation
- Rubber-coated handle
- Metabo S-automatic torque limiting clutch
- Metabo winding protection grid
- Auto-stop carbon brushes
- Brush wear indicator



	Electronic Combination Hammer KHE 26	Electronic Combination Hammer KHE 26 Contact	Electronic Combination Hammer KHE 28
<b>Special advantages</b>			
▪ Metabo "Contact" Technology		•	
▪ Metabo CODE! System: electronic anti-theft system, activated by CODE! key (accessory)	•		•
▪ Vario Constamatic (VC) full-wave electronics		•	
▪ Vario Tacho Constamatic (VTC) full-wave electronics	•		•
▪ Thumbwheel for preselection of speed		•	
▪ No-volt release switch	•		•
<b>Comparative device characteristics</b>			
Torque	16 Nm	16 Nm	20 Nm
Drilling capacity in			
- Concrete with hammer drill bits	26 mm	26 mm	28 mm
- Concrete with router bits			
- Concrete with TCT bits			
- Masonry with TCT bits	65 mm	65 mm	80 mm
No load speed	0 - 1.000 /min	0 - 1.050 /min	0 - 1.000 /min
Rated input power	800 W	800 W	1.010 W
Output power	450 W	450 W	610 W
Rated load speed	1.000 /min	830 /min	1.000 /min
Maximum impact rate	4.600 /min	4.830 /min	4.600 /min
Maximum single-blow energy	2,3 J	2,3 J	2,5 J
Collar diameter	43 mm	43 mm	43 mm
Bit retainer	SDS-plus	SDS-plus	SDS-plus
Weight (without mains cable)	2,7 kg	2,7 kg	2,7 kg
<b>Standard equipment</b>	Hammer chuck for tools with SDS-plus shank end, quick-action keyless chuck for tools with cylindrical shank end, rubber-coated side handle, drilling depth guide, carry case	Hammer chuck for tools with SDS-plus shank end, rubber-coated side handle, drilling depth guide, carry case	Hammer chuck for tools with SDS-plus shank end, rubber-coated side handle, drilling depth guide, carry case
<b>Type</b>	KHE 26	KHE 26 Contact	KHE 28
<b>Order no.</b>	6.00337 ■	6.00244	6.00338 ■

ANGLE GRINDERS

METAL PROCESSORS

HAMMERS

IMPACT DRILLS

DRILLS

SCREWDRIVERS

WOOD SANDING MACHINES

ROUTERS AND PLANERS