





# Constant Voltage Led Power Supply

## ECP30 series



### Features

- Input Voltage: 200 – 240Vac
- Output Power: 30W
- Compact and light-weight plastic case
- Working Temperature: -20C to +45C
- Protections: short circuit/overload/overheat
- Power factor corrected
- 1 year warranty



Part number	Voltage	Load	Max Output Current	PF	L x W x H
764-7158	12	0-30W	2.50A	>0.9	123 x 45 x 20 mm
764-7167	24	0-30W	1.25A		

### Mechanical specification

Designed to meet Safety:

EN61347-1  
EN61347-2-13  
EMI to EN55015  
EMS to:  
EN61000-3-2  
EN61000-3-3  
EN61547

