


BGA452Z

Battery Type	Lithium-ion
Charging Time	22 min
Body only machine	1
Voltage	18 v
Noise sound pressure	73 dB(A)
Noise K factor	3 dB(A)
Max Wheel Diameter	115 mm
No Load Speed	10000 rpm
Vibration K factor	1.5 m/sec ²
Vibration: Artificial Wheel	8.5 m/sec ²
Net weight	2.3 kg



- 22 minute charge time with the air cooled Makstar Optimum Charging System.
- Lithium-ion batteries have greater life spans than their Ni-MH or Ni-Cad counterparts giving 430% greater run time.
- Lithium-ion's 40% weight saving means 18 volt power can be obtained by a battery that weighs the same as a 12 volt Ni-MH battery.
- 4 pole motor.
- Anti-restart function with warning lamp.
- Capable of using wheels or discs for mains grinders.
- Easy grip body.
- Electronic current limiter with warning lamp.
- High comfort grips.