



ENGLISH

Datasheet

RS Pro Stainless Steel IP66 Junction Box, 150 x 80 x 150mm, Natural

RS Stock No: **749-1860**



Product Details

RS Pro junction box in natural colour, is made of stainless steel and measures 150 x 80 x 150 mm. It has IP66 enclosure. This heavy duty terminal box is designed for housing DIN rail terminals and accessories. It is constructed from 1.2 mm AISI 304 natural finish stainless steel and is fitted with a black neoprene gasket.

Features and Benefits

- Lids with black neoprene gasket and 4 x M6 captive hexagon headed screws
- Multiple DIN rail fixing points, M5
- External M6 earthing stud
- Material 304/1.4301 stainless steel
- IP66 rated
- Operating temperature -20 to +110°C



Specifications:

Colour	Natural
Dimensions (L x W x H)	150 x 80 x 150 mm
Height	150 mm
IP Rating	IP66
Length	150 mm
Material	Stainless Steel
Mounting Type	Wall
Width	80 mm
Wall Thickness	1.2 mm