






NUMBER C-179096
METRIC
3rd ANGLE PROJECTION



注: Δ E面より2mmの範囲で測定
 Δ 相手ハウジングと所定の機能を満足して嵌合できること
3 プリント基板への取付は、JIS B1115又は1122,M3X6ナベ
(2種又は4種)のタッピンネジで締付けた後ハンダ付する
(締付トルク: 4kg-cm以下)
 Δ 回路番号: 右図参照のこと

NOTES: Δ TO BE MEASURED BETWEEN E AND 2
 Δ TO BE MATE WITH PLUG HSG SMOOTHLY
3 TO BE USE M3 TAPPING SCREW JIS B1115 OR 1122
(TYPE2 OR 4) BEFORE SOLDER
 Δ CIRCUIT NUMBER



					1-8 Pos. (全個)		白 (WHITE)		8Pcs. HORIZONTAL TYPE CAP HSG 水平型キャップハウジング		179096-1	
					PRE-TINNED 錫メッキ		HOUSING COLOR		名称 (NAME)		型 番 (P/N)	
					回路番号 CIRCUIT NUMBER		ハウジング色					
					Copyright © 1993 AMP (Japan) LTD. ALL RIGHTS RESERVED.						AMP AMP (JAPAN) ,LTD. Tokyo, Japan	
					WIRE RANGE mm ² (AWG)		INSULATION DIA mm		NAME .070 SERIES MULTI-LOCK I/O CONN. 8POS. (H) CAP HSG			
					MATERIAL BRASS		FINISH TIN 錫メッキ		GENERAL TOLERANCE 0<L<10 : ±0.2 10<L<30 : ±0.25 30<L<100 : ±0.3 ANGLES : ±3°		SIZE LOC NUMBER A3 J C-179096	
O RELEASED FJ88-0264-93 Y.T.S.M. S-25-73					DR. Y. Tanaka 25-MAY-93		DE Y. Tanaka 25-MAY-93		SCALE 2-1		REV. 0	
					CHK S. MAKINO		APP. S. MAKINO				SHEET - OF -	
LTR REVISION RECORD					DR		CHK		DATE			

CUSTOMER DRAWING

CUSTOMER DRAWING

PRINT DISY

REV. 10/93

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT