


NO	DESCRIPTION	DATE
1	4.50 $\longrightarrow$ 4.5	10.03.16'



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-4 GHz
1.2 NOMINAL IMPEDANCE: 50 OHMS
1.3 VOLTAGE RATING: 500 VOLTS MAX.

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
2.2 CENTER CONTACT: BERYLLIUM COPPER PER ASTM B196 UNS C17300
2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS






- 3.1 SEE BELOW TABLE FOR DETAILS.**

4.0 MECHANICAL

- 4.1 FOR USE WITH RG58U OR SIMILAR STYLE CABLE
4.2 CABLE ATTACHMENT: OUTER: CLAMP, INNER: SOLDER

5.0 ENVIRONMENTAL

- 5.1 OPERATING TEMPERATURE RANGE: -65° C TO +165° C**



8	WASHER	BRASS	1	SILVER 70 μ " MIN.
7	NUT	BRASS	1	SILVER 70 μ " MIN.
6	GASKET	SILICONE	1	RED
5	BRAID CLAMP	BRASS	1	SILVER 70 μ " MIN.
4	INSULATION	TEFLON	1	NONE
3	CENTER CONTACT	BERYLLIUM COPPER	1	SILVER 70 μ " MIN.
2	INSULATION	TEFLON	1	NONE
1	BODY	BRASS	1	SILVER 70 μ " MIN.
NO	DESCRIPTION	MATERIAL	Q' TY	FINISH



APPROVED

by _____ DATE: _____

DESCRIPTION		BNC STRAIGHT JACK CLAMP									
製圖	DRAWN	TOLERANCE		品名	13-07-5 T.S.S 58U			日期	DATE	版次	REV.
	Yoko			\ROHS COMPLIANT (50u)			03.20.93'		B-1		
檢圖	CHECK	.XX	±0.1	單位	UNIT	DWG.NO. 13-0061(13-007-05-01)					
	Arc				mm(in)						
認定	APPROVAL	.XXX	±0.05	比例	SCALE						
	Angela				ANGLE						