



A unique, patented alarm bell designed for use in fire, security and other signalling systems. The combination of a miniature solenoid with an integrated control circuit allows excellent sound coverage, minimum current consumption and increased reliability. The improved aesthetics make the bell suitable for all applications including the most prestigious locations.


Features

- Modern design
- Simple installation
- Weatherproof kit option
- High sound output

Benefits

- Suitable for all locations
- Easy to fit
- Provides protection up to IP33C
- Delivers up to 95dB(A)

Dimensions



Technical Specification

Voltage	24Vdc
Current	24 Vdc 25 - 35mA
Sound Output	95dB(A)
Monitoring	Reverse polarity (dc only)
Temperature	-10°C to +55°C (Indoor) -25°C to +70°C (Outdoor)
Protection	IP21C, IP33C (WP)
Construction	Gong - Steel, Base - Polycarbonate
Weight	24 Volt 1.1Kg
Colours	Gong - Red and Grey Base - Black

FB Bell Grey



Catalogue Numbers

Reference	Cat No	Description
FB/12/RED	500001FULL-0001	Electronic Solenoid Bell 12 Volts DC, Red
FB/024/R	502001FULL-2001	Electronic Solenoid Bell 24 Volts DC, Red

