


# D-SUB sleeve housings - VS-09-T-20-1-S-A - 1655661

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

D-SUB sleeve housing, shell size 1, shielded, IP20 degree of protection



## Key commercial data

Packing unit	1 pc
GTIN	 4 046356 029551
Weight per Piece (excluding packing)	12.6 g
Custom tariff number	85389099
Country of origin	Hungary

## Technical data

### Mechanical characteristics

External cable diameter	4 mm ... 8.5 mm
Cable exit	Angled
Color	Bare metallic

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
Degree of protection	IP20

### Material data

Inflammability class according to UL 94	V0
Housing material	ABS
Housing surface material	Metal-plated

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816

# D-SUB sleeve housings - VS-09-T-20-1-S-A - 1655661

## Classifications

### eCl@ss

eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

### ETIM

ETIM 2.0	EC001133
ETIM 3.0	EC001133
ETIM 4.0	EC001133
ETIM 5.0	EC001133

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

## Drawings

Dimensioned drawing

