

Datasheet

RS Pro Insulated Crimp Piggyback Terminal, 6.35 x 0.8mm, 0.5mm² to 1.5mm², 22AWG to 16AWG, Red
RS Stock No: **267-4322**



Product Details

RS Pro insulated crimp piggyback terminal in red colour, has 6.35 x 0.8 mm tab size and 0.5 mm² to 1.5 mm², 22 AWG to 16 AWG wire size. It has a range of insulated piggyback crimp terminals with a copper sleeved barrel and nylon or flared vinyl insulation. This insulated piggyback crimp wire connector is colour coded for use with different wire sizes and accept a variety of tab dimensions.

Features and Benefits

- Insulated piggyback crimp terminals with a copper sleeved barrel with nylon or flared vinyl insulation
- Insulated piggyback crimp wire connectors are colour coded for use with different wire sizes and accept a variety of tab dimensions
- Red 0.5 - 1.0 mm², blue 1.5 - 2.5 mm² and yellow 2.5 - 6.5 mm²

**Specifications:**

Colour	Red
Contact Material	Brass
Insulation	Insulated
Insulation Material	Nylon
Shrouded	Unshrouded
Maximum Wire Size (AWG)	16 AWG
Maximum Wire Size (mm ²)	1.5 mm ²
Minimum Wire Size (AWG)	22 AWG
Minimum Wire Size (mm ²)	0.5 mm ²
Overall Length	23 mm
Tab Size	6.35 x 0.8 mm
Tab Thickness	0.8 mm
Tab Width	6.35 mm
Wire Size	22 to 16 AWG
Current Rating	3 to 10 A
Temperature Rating	+105°C
Type	Double Crimp
Voltage Rating	600 V