



mecalectro

Small linear solenoid for standard use – 8.M17.02.62 (Push)



Stroke: 18 mm

Force at beginning of stroke (FM: 100/25/5%):
5/15/60 N

Force at end of stroke (FM: 100/25/5%):
40/90/140 N

Power Consumption (FM: 100/25/5%):
19/70/307 W

Total mass: 1100 g

Degree of protection / Energetic class: IP 00 / B

Standard supplies: 24Vcc

Possibles supplies: From 6 to 250Vcc

Duty Cycle: Permanent, impulses (100 / 40 / 25 / 15 / 5 %)

Standard: NF C 79300

Examples of applications: various automations, positioning, multiple locks