

Linear Fluorescent Lamps

Wattage [W]	Length [mm]	Diameter [mm]	Product Description	Product Code	Initial Lumen (at 25°C) [lm]	Colour Type	CCT [K]	CRI [Ra]	Rated Average Life (3-hr cycle) [h]	EEC	Energy Consumption [kWh]	Pack Qty
15	437.4	26	F15W/T8/830/POLYLUX	23248	950	Warm White	3,000	80+	15,000	B	19	25
15	437.4	26	F15W/T8/835 POLYLUX	78133	950	White	3,500	80+	15,000	B	19	25
15	437.4	26	F15W/T8/840/POLYLUX	23249	950	Cool White	4,000	80+	15,000	B	19	25
15	437.4	26	F15W/T8/860/POLYLUX	78131	900	Daylight	6,400	80+	15,000	B	18	25
18	589.8	26	F18W/T8/827/POLYLUX	62560	1,350	Extra Warm White	2,700	80+	15,000	A	22	25
18	589.8	26	F18W/T8/830/POLYLUX	62559	1,350	Warm White	3,000	80+	15,000	A	22	25
18	589.8	26	F18W/T8/835/POLYLUX	62534	1,350	White	3,500	80+	15,000	A	22	25
18	589.8	26	F18W/T8/840/POLYLUX	62558	1,350	Cool White	4,000	80+	15,000	A	22	25
18	589.8	26	F18W/T8/860/POLYLUX	62557	1,250	Daylight	6,400	80+	15,000	A	22	25
30	894.6	26	F30W/T8/830/POLYLUX	18141	2,450	Warm White	3,000	80+	15,000	A	37	25
30	894.6	26	F30W/T8/835/POLYLUX	78132	2,450	White	3,500	80+	15,000	A	37	25
30	894.6	26	F30W/T8/840/POLYLUX	18142	2,450	Cool White	4,000	80+	15,000	A	37	25
30	894.6	26	F30W/T8/860/POLYLUX	12607	2,300	Daylight	6,400	80+	15,000	A	36	25
36	1,199.4	26	F36W/T8/827/POLYLUX	62554	3,350	Extra Warm White	2,700	80+	15,000	A	42	25
36	1,199.4	26	F36W/T8/830/POLYLUX	62553	3,350	Warm White	3,000	80+	15,000	A	42	25
36	1,199.4	26	F36W/T8/835/POLYLUX	62532	3,350	White	3,500	80+	15,000	A	42	25
36	1,199.4	26	F36W/T8/840/POLYLUX	62551	3,350	Cool White	4,000	80+	15,000	A	42	25
36	1,199.4	26	F36W/T8/860/POLYLUX	62552	3,250	Daylight	6,400	80+	15,000	A	43	25
58	1,500	26	F58W/T8/827/POLYLUX	62550	5,200	Extra Warm White	2,700	80+	15,000	A	68	25
58	1,500	26	F58W/T8/830/POLYLUX	62549	5,200	Warm White	3,000	80+	15,000	A	68	25
58	1,500	26	F58W/T8/835/POLYLUX	62531	5,200	White	3,500	80+	15,000	A	68	25
58	1,500	26	F58W/T8/840/POLYLUX	62548	5,200	Cool White	4,000	80+	15,000	A	68	25
58	1,500	26	F58W/T8/860/POLYLUX	62547	5,000	Daylight	6,400	80+	15,000	A	68	25
70	1,763.8	26	F70W/T8/835/POLYLUX	62572	6,000	White	3,500	80+	15,000	A	81	25
70	1,763.8	26	F70W/T8/840/POLYLUX	62573	6,000	Cool White	4,000	80+	15,000	A	81	25

T8 covGuard™ PolyLux XLR™ - G13 Cap

18	589.8	26	F18W/T8/835 CVG	17204	1,310	White	3,500	80+	15,000	A	22	25
18	589.8	26	F18W/T8/840 CVG	17205	1,300	Cool White	4,000	80+	15,000	A	22	25
36	1,199.4	26	F36W/T8/835 CVG	17202	3,250	White	3,500	80+	15,000	A	42	25
36	1,199.4	26	F36W/T8/840 CVG	17209	3,250	Cool White	4,000	80+	15,000	A	42	25
58	1,500	26	F58W/T8/835 CVG	99590	5,050	White	3,500	80+	15,000	A	68	25
58	1,500	26	F58W/T8/840 CVG	99591	5,050	Cool white	4,000	80+	15,000	A	68	25

T8 covGuard lamps can be used both in open and closed fixtures.

Wattage [W]	Volt [V]	Product Description	Rated Life (switching cycles)	Product Code	Pack Qty
Starter					
Single 4-65W	110-130V	155/501/4/65W/UNIV/BX	10,000	36536	250
Single 4-65W	110-130V	155/501/4/65W/UNIV/IND	10,000	36537	2,000
Series 4-8W, 15-22W	220-240V	155/200/4-22W/TANDEM/BX	10,000	36711	250
Series 4-8W, 15-22W	220-240V	155/200/4-22W/TANDEM/IND	10,000	36714	2,000
Single 75-125W	110-130V	155/800/75-125W/BX	10,000	37864	250
Single 75-115W	110-130V	155/801/75-115W/BX	10,000	37975	250
Single 75-115W	110-130V	155/801/75-115W/IND	10,000	37974	2,000
Series 4-8W, 15-22W	220-240V	155/200 4-22W/TANDEM/BX	8,000	64085	250
Series 4-8W, 15-22W	220-240V	155/200 4-22W/TANDEM/IND	8,000	64086	2,000
Single 4-65W	110-130V	155/500 4-65W/UNIV/BX	8,000	64087	250
Single 4-65W	110-130V	155/500 4-65W/UNIV/IND	8,000	64088	2,000

