

Loopermat



Soft compounded PVC looped matting
 Traps dirt, debris and moisture
 UV stabilised to prevent fading
 Fire tested to DIN 4102 (B1)
 Easy to clean – simply shake mat to free debris
 Available as Heavy Unbacked and Medium Backed
 product heights: 9mm (Backed) & 14mm (Unbacked)

Mat Size (m.) width x length	Weight Kg.	Packaging Size CM	Packaging Type	Packaging Volume (m.)	Packaging Quantity	Colour	Part Code
0.9m x per linear metre (max length 9m)	4	5 x 5 x 96	Roll		1	Grey	LU060909C
					1	Red	LU030909C
					1	Green	LU040909C
					1	Blue	LU020909C
					1	Grey (Backed)	LB060909C
					1	Brown (Backed)	LB050909C
1.2m x per linear metre (max length 9m)	7	5 x 5 x 120	Roll		1	grey	LU060912
					1	Red	LU031209C
					1	Green	LU041209C
					1	Blue	LU021209C
					1	Grey (Backed)	LB061209C
					1	Brown (Backed)	LB051209C

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that matting products may be subject to a degree of shrinkage when installed into some applications.