



ENGLISH

Datasheet

Stock No: 691-987

RS Pro Steel Abrasive Circular Brush, 6000rpm, 76mm Diameter



Image representative of range

Product Details

Refill Wheel

Single section 0.30mm (32swg) steel wire brushes

Suitable for use on bench or pedestal grinding machines

Brushes can be assembled onto the grinding machine arbor individually or in multiples, for adapting to the profile of a specific workpiece as well as for providing various face widths



ENGLISH

Specifications:

Bristle Material	Steel
Bristle Length	17mm
Diameter	76mm
Fixing Size	6mm
Fixing Type	Arbor
Maximum Safe Speed	6000rpm