



GE
Lighting



Reflector

OT 42W HALO R80/E27 240V GE TRBX
1/6MIC

95117

Product information

GE's HaloReflector range is a direct replacement for regular incandescent lamps offering a crisp white light. These bulbs are the environmentally friendly solution for those who prefer the features and light quality associated with incandescent bulbs.

- Last twice as long and consume up to 30% less electricity than corresponding incandescent lamps.
- Provide instant-on, full light output at start-up and lumens are maintained throughout the life of the product.
- Unlike some compact fluorescent products, these lamps are 100% retrofit with the incandescent lamps they replace.
- Can be used with dimming switches.
- Environmentally friendly with no lead or mercury.
- Up to 2,000 hours life
- Excellent colour rendering, light close to natural (100% CRI)

- More than 90% lumen maintenance over life
-

Product data

Cap/Base	E27
Bulb Shape	Reflector
Bulb Diameter [mm]	80
Maximum Overall Length [mm]	116
Net weight per piece [g]	37
Gross weight per piece [g]	96
Brand	General Electric (GE)

Performance data

Nominal correlated colour temperature (CCT) [K]	2600
Rated Life [h]	2000
Nominal power [W]	42
Nominal lamp voltage [V]	240

Electrical data

Dimming Capability	Yes
--------------------	-----

Logistic data

DUN Code	10043168951170
EAN Code	0043168765381
Pack Quantity	6
Inner pack type	TRAY
Outer pack type	OUTER BOX
Layer quantity	150 EUR, 180 UK
Layer quantity EUR	150
Layer quantity UK	180
Pallet quantity EUR (PC)	1350
Pallet quantity UK (PC)	1620
Outer case size	240 x 160 x 110 (mm)
Product status	Available

Application areas



Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[Halogen Lamps Spectrum Catalogue \(PDF\)](#)

[Lighting design tools & calculators \(HTTP\)](#)