



92730 - OT Q50MR16 240V GU10 FL GEST BX1/10 MIC

• Specifications

General characteristics:

Wattage [W]	50
Voltage [V]	240
Cap/Base	GU10
Bulb Shape	MR
Bulb Diameter [mm]	50
Colour temperature [K]	2800
Colour Rendering Index (CRI) [Ra]	100
Rated Life [h]	2000
Dimming Capability	Yes
Coil type	CC-2V
Beam Angle [°]	36
Center Beam Candlepower [cd]	600
Maximum Overall Length [mm]	55
DUN Code	20043168927301
EAN Code	0043168927307
Net weight per piece [g]	48
Gross weight per piece [g]	63
Pack Quantity	10
Inner pack type	BOX
Layer quantity UK (PC)	360
Pallet quantity EUR (PC)	3300
Pallet quantity UK (PC)	5400
Outer case size	270 x 110 x 66 (mm)
Brand	General Electric (GE)
Product status	Available