

Datasheet

Stock No: 203-981

Prominent Indicator Panel Mount, 14mm Mounting Hole Size, Red LED, Solder Tab Termination, 10 mm Lamp Size, 2 V dc



Product Details

LED Indicator, 14mm Mounting

Brought to you under the trusted RS Brand, this LED indicator has a recessed diffused epoxy style lens within a prominent chrome bezel. The indicator has a compact robust body that terminates with convenient solder tabs, for ease of installation. Offering a low power consumption and long life, LED indicators are suitable for a variety of equipment needs.

Features and Benefits:

- 10mm coloured diffused epoxy lens
- 16mm chrome bezel
- 0.11in. (2.8 x 0.8mm) crimp terminals
- 2.8 x 0.8 insulated crimp/cable assembly 300mm long available separately with red or black cable
- Life expectancy: 60000 Hours
- Operating temperature: -20 to +70°C

Supplied with

fixing nut and washer.

10mm - 15.8mm Mounting

All products have a reverse voltage of 5V.

Specifications:

ENGLISH

Voltage Rating	2 V dc
Light Output Colour	Red
Mounting Hole Size	14mm
Lamp Size	10 mm
Length	47 mm
Type	Panel Mount
Lamp Type	LED
Termination Type	Solder Tab
Bezel Style	Prominent
Bezel Colour	Chrome
Intensity	7500 mcd
Current Rating	20 mA

Dimensions (mm):

