




5

4

3

2

1





SPECIFICATIONS

FREQUENCY (MHz)	ATTENUATION (dB)
5	0,5
10	1
50	2,5
100	3
500	3,5
1000	4

Operating voltage < 250 V AC
 Working current < 7,5 A
 Insulation resistance > 1GΩ
 Contact resistance < 15 mΩ
 Dielectric withstanding voltage 500 V AC / minute

Solder bucket termination inner diameter: 1,20 mm

						 All Dim. in mm Orig. Size DIN A 4	D-Sub, male, straight, 9 poles, tin plated shell with dimples, solder buckets, ferrite filter	Maßstab/ Scale 1,5:1	
				Detail.	11/06/09				PK
				Insp.					
				Stand.					
09 64 121 7800	Au Flash	EC00332	11/06/09	PK	HARTING EURL F-95972 Paris		 TB 09 64 121 7800	Blatt/ Page 1 / 1	
Part number	Performance level	Mod.	Dot.	Name					Sub.

D

C

B

A