

LED LENSER® H3 HEAD LAMP

Popular lightweight head torch with an integrated non-dazzle dimmer switch that makes it especially helpful for localised hands-free lighting around the home or workplace. Instead of a single super-strength light it has three energy efficient LEDs delivering a bright and comfortable 60 lumens of light up to 31 metres with a potential burn time of up to 62 hours when used on the lowest lumen setting. On the back of the comfortable elasticated headband there is a battery pack with an integrated variable control lever that allow the user to dim the lighting; thereby creating a softer light for 'nearer' tasks like reading, illuminating a pathway, viewing maps or inspecting utility meters. The stretch-safe Flexi-cable insures robust use and there is also the facility to swivel the lamp direction within 90 degrees, just enough to save having to turn your head an awkward angle – let the light do the work instead! Includes 3 x AAA batteries, and belt pouch.

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- Fixed focus multi-LED Head Lamp
- Three energy efficient LED light chips producing a flawless single white light beam
- State-of-the-art, reliable German engineering
- Swivelling lamp head for directional 90° lighting
- Integrated dimmer switch enable light adjustment down to 3.5 lumens thus conserving battery life
- Lightweight, comfortable and adjustable head strap
- Stretch safe flexi-cable
- Water and dust resistant. IPX54

Technical Information

Power: 60 lumens max

Run Time: up to 62 hours

Beam Distance: up to 31m

Weight: 114grams

Supplied with : Belt Pouch and Duracell® batteries (3xAAA)

Code	Colour	Packaging	Barcode
1041TP	Black	Test-It	4029113104166