

BOSS

This model is also available in our prescription range (see specialist catalogue) and provides extensive protection for most circumstances. The straight temples feature rubber tips for enhanced grip and extra stability and comfort.

Ref. BOSSPSI



Europe Bollé Safety
95 Rue Louis Guérin
69100 Villeurbanne - France
tel: 00 33 (0) 4 78 85 23 64
fax: 00 33 (0) 4 78 85 28 56
contact@bolle-safety.com

U.K. Bollé Safety
Unit C83 - Barwell Business Park
Leatherhead Road - Chessington
Surrey - KT9 2NY
tel. 00 44 (0)208 391 4700
fax 00 44 (0)208 391 4733
e-mail : sales@bolle-safety.co.uk

STANDARDS MARKINGS :

Product ref.	LENSES												FRAMES												
		Bollé Protection logo	Optical quality			 Mechanical Risks			 Electrical Risks	 Thermal Risks	Coatings (Optional marking K: anti-scratch N: anti-fog)	CE logo	Bollé Protection logo	Standards	 Chemical Risks	 Electrical Risks	 Mechanical Risks	 Thermal Risks	CE logo						
	EN 170 - UV		Permanent wear	Intermittent wear	Short period	Low energy impact 45 m/s	Medium energy impact 120 m/s	High energy impact 190 m/s	Extremes of temperature impact	Electric arc short circuiting	Molten metals and hot solids				anti-scratch anti-fog	Liquid drops	Large dust particles > 5 microns	Gas and fine dust particles < 5 microns		Electric arc short circuiting	Low energy impact 45 m/s	Medium energy impact 120 m/s	High energy impact 190 m/s	Extremes of temperature impact	Molten metals and hot solids
BOSSPSI	2C-1,2		1			F	N/A	N/A		N/A	T	 GKN CE			EN 166	N/A	N/A	N/A	N/A	F	N/A	N/A	T	N/A	

N/A: Non applicable

 BOSSPSI


CHARACTERISTICS :

Lenses	PC - 2,2 mm - Curve 8
Frame	PC
Temples	PC + TPR
Strap	Non applicable
Foam	Non applicable
Spare lenses	No

PACKAGING AND EAN 13 CODE :

	BOSSPSI
→ individual plastic bag	3660740000714
→ 10 safety spectacles per box	3660740100711
→ 240 safety spectacles per outer pack	3660740200718

 Notified
 laboratories
 for
 certification :

BSI
 Product Services

DIN
INSPEC