

(4) $\phi 1.4$ (.055) MIN.
(1) $\phi 1.1$ (.043) MIN.

10.1 (.398)

10.1 (.398)

MOUNTING HOLE

(.033)
0.85

9.25 (.364) REF.

(.033)
0.85

12 (.472) REF.

12 (.472) REF.

$\phi 1.00$ (.039)

2.2 (.087)

10.8 (.425)

17.0 (.669)

$\phi 11.0$ (.433)

1.1 FREQUENCY RANGE: DC-4 GHz
1.2 NOMINAL IMPEDANCE: 50 OHMS
1.3 VOLTAGE RATING: 500 VOLTS MAX. $\triangle$
1.4 VSWR: 1.5 MAX. $\triangle$

2.1 BODIES: BRASS PER JIS-C3604
2.2 CENTER CONTACT: BERYLLIUM COPPER PER ASTM B196 UNS C17300
2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.1 SEE BELOW TABLE FOR DETAILS.

4.1 OPERATING TEMPERATURE RANGE: -65° C TO +165° C



APPROVED by DATE:

DESCRIPTION			BNC STRAIGHT PCB MOUNT JACK RECEPTACLE									
製圖	DRAWN	TOLERANCE		品名	13-22-5 T.S.S			日期	DATE		版次	REV.
	Yoko			TITLE	\ROHS COMPLIANT (50μ)		12.09.92'		B-2			
檢圖	CHECK	.XX	±0.1	單位	UNIT	DWG.NO.		13-0172				
	Arc				mm(in)							
認定	APPROVAL	.XXX	±0.05	比例	SCALE							
	Jenny				ANGLE							