




ROHS-COMPLIANT

LTR	REV.	DESCRIPTION	DATE


USB 3.0 A/F
INS: BLUE(PT 300C)



USB 3.0 A/F
INS: BLUE(PT 300C)



P2



NOTE:

1.PCB

2.CONNECTOR:

P1&P2: USB 3.0 A FEMALE DIP TYPE 9PIN CONTACT:15u",SHELL:NI-PLATED.

3.HOOD: MOLDED TYPE, PVC 45P, COLOR:BLACK(NK-K01)

4.ELECTRICAL TEST:

<1> 100% OPEN SHORT & MIS WIRE TEST

<2> CONTACT RESISTANCE 3 OHM MAX.

<3> INSULATION RESISTANCE 5M OHM MIN

5.PACKING:EACH PC / SMALL BLISTER + ROLINE BACK CARD

+ BAR CODE LABEL

20 PCS / INNER CARTON; 2 INNER CTN / MASTER CTN.

PIN OUT

P1	PIN OUT	P2
1	_____	1
2	_____	2
3	_____	3
4	_____	4
5	_____	8
6	_____	9
7	_____	7
8	_____	5
9	_____	6
SHELL	_____	SHELL

Tolerance	Inch	M/M
.X	.015	.30
.XX	.010	.10
.XXX	.005	.05

Draw
FANNIE 08/27/10'
Check
Engr

Rotronic co., LTD.

Title
USB 3.0 AF TO AF ADAPTER

Customer P/N: 12.03.2991

App'd Customer: T-RAG

Scale NONE Units m/m Third Angle Projection

Dwg No. 160-1742 REV:A Sheet 1/1