

CHERRY DW 8000



Models may vary from the image shown

Top quality, puristic designer desktop set

The CHERRY DW 8000 is state-of-the-art CHERRY technology in a pure, modern design. Beautiful, flat, high-quality. Today's way of typing and clicking.

Key benefits

- Ultra-flat wireless keyboard with 5 hotkeys
- Simple installation; no technical knowledge required
- 3-button mouse with an infrared sensor and adjustable resolution (1000/2000 dpi)
- Battery status display in mouse and keyboard
- Interference-free, wireless 2.4 GHz technology (with a range of approx. 10 m)
- USB receiver

Technical Data:

Layout (country or language):

Product dependant, see table "Models"

Housing colour:

white/silver

Key colour:

white

Weight (product):

approx. 722 g (keyboard with battery), approx. 127 g (mouse with battery), approx. 6 g (receiver)

Total weight (with packaging):

approx. 1184 g

Transmission range:

approx. 10 m

Frequency range:

2.400 GHz - 2.4835 GHz

Storage Temperature:

-20°C to 60°C

Operating Temperature:

0°C to 40°C

Current Consumption:

typ. 1.5 mA (keyboard), typ. 5 mA (mouse), typ. 30 mA (receiver)

Interface:

- USB

Product approvals:

- c-tick 
- UL 
- CE 
- FCC 

System requirements:

- USB connection

Delivery Volume:

- 1 signal receiver
- Operating instructions in hard copy
- 4 batteries (type AAA)
- 1 wireless keyboard
- 1 infrared wireless mouse

Dimensions (product):

441 x 165 x 18 mm (keyboard), 107 x 60 x 27 (mouse), 40.2 x 18.2 x 4.5 mm (receiver)

Packaging dimensions:

approx. 580 x 230 x 35 mm

Mouse:

- Scanning: Infrared
- Resolution: 1000 / 2000 dpi (adjustable)
- Number of Keys: 3
- Mouse wheel design: Scroll wheel with key function
- Design: Symmetrical
- Connection: wireless
- Housing colour: white/silver
- Key colour: silver

Keyboard:

- Protection class: Protected against splash water
- Service life, standard key: > 10 million key operations
- Inscription layout: Standard
- Number of Keys: Product dependant, see table "Models"
- Number of additional keys: 5

Packaging Unit:

- Number of products in the master package: 6
- Number of master packages per pallet: 24

Warranty:

2 years

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.

Models:

(possible country/layout versions, others available on request)

	Product name	Order number	EAN code	Layout (country or language)	Number of Keys
1	CHERRY DW 8000	JD-0300BE-	4025112080074	Belgium	104+5
2	CHERRY DW 8000	JD-0300CH-	4025112080081	Switzerland	104+5
3	CHERRY DW 8000	JD-0300DE	4025112076473	Germany	104+5
4	CHERRY DW 8000	JD-0300ES-	4025112080128	Spain	104+5
5	CHERRY DW 8000	JD-0300EU	4025112076480	US English with EURO symbol	103+5
6	CHERRY DW 8000	JD-0300FR-	4025112080098	France	104+5
7	CHERRY DW 8000	JD-0300GB-	4025112080104	UK	104+5
8	CHERRY DW 8000	JD-0300IT-	4025112080111	Italy	104+5
9	CHERRY DW 8000	JD-0300PN-	4025112080609	Pan-Nordic	104+5