

Basic terminal block - URELG 3 - 2820136

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




Basic termination blocks with screw connection for NS 32 and NS 35/7.5 DIN rail, with end cover, for ST-REL..., ST-OV... and ST-OE... plugs, 3-pos.

The illustration shows versions with a different no. of positions



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 076788
Weight per Piece (excluding packing)	30.58 g
Custom tariff number	85369010
Country of origin	Germany

Technical data

Dimensions

Width	20.8 mm
Height	42.5 mm
Depth	112 mm

General

Number of positions	3
Nominal voltage U_N	400 V (voltage is determined by the coupling connector.)
Nominal current I_N	16 A (current is determined by the coupling connector.)
Color	gray
Insulating material	PA

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²

Basic terminal block - URELG 3 - 2820136

Technical data

Connection data

Conductor cross section stranded max.	4 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Connection method	Screw connection
Stripping length	9 mm
Screw thread	M3

Classifications

eCl@ss

eCl@ss 4.0	27141127
eCl@ss 4.1	27141127
eCl@ss 5.0	27371603
eCl@ss 5.1	27371603
eCl@ss 6.0	27371603
eCl@ss 7.0	27371603
eCl@ss 8.0	27371603

ETIM

ETIM 2.0	EC001456
ETIM 3.0	EC001456
ETIM 4.0	EC001456
ETIM 5.0	EC001456

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Approvals

Approvals

Approvals

GOST / DNV

Ex Approvals

Basic terminal block - URELG 3 - 2820136

Approvals

Approvals submitted

Approval details

GOST 

DNV

Accessories

Accessories

Bridge


Wire bridge - DB 50- 90 GY - 2820929

Wire bridge, Color: gray



Wire bridge - DB 50- 90 BK - 2820916

Wire bridge, Color: black



Wire bridge - DB 50- 90 BU - 2821180

Wire bridge, Color: blue



End block

Basic terminal block - URELG 3 - 2820136


Accessories

End clamp - E/UK - 1201442




End clamp, for assembly on NS 32 or NS 35/7.5 DIN rail

Drawings



Basic terminal block - URELG 3 - 2820136

Schematic diagram



- 1 = Coupling connector
- 2 = Coding
- 3 = Cover
- 4 = Basic termination block