


Deep groove ball bearings, single row, unsealed



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN	C_0	kN	r/min		kg	-
15	35	11	8,06	3,75	0,16	43000	28000	0,045	6202 *



Calculation factors

k_f 0,025
 f_0 13