

Crimping pliers - CRIMPFOX-CX 10,54 - 1212097

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, for coaxial connectors, 10.54 mm, 2.54 mm, HEX crimp

Why buy this product

- Lateral conductor entry
- Unlockable pressure lock



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 453974
Weight per Piece (excluding packing)	667.9 g
Custom tariff number	82032000
Country of origin	Sweden
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	256 mm
Height	68 mm
Width (a)	25 mm

General

Color	black
Compression	HEX crimp
Type of contact	Coaxial connectors
Designation	Crimping position 1
	Crimping position 2
	Crimping position 3
Die station	Crimping position 4

Crimping pliers - CRIMPFOX-CX 10,54 - 1212097

Technical data

General

	Crimping position 5
--	---------------------

Classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Crimping pliers - CRIMPFOX-CX 10,54 - 1212097

Accessories

Accessories

Die

Replacement die - CRIMPFOX-CX 10,54/DIE - 1212291



Spare die for CRIMPFOX-CX 10,54

Mounting material

Replacement spring - CRIMPFOX/ SPR-1 - 1212069



Spare recuperating spring