






LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
J	—	P4		ADDED 3-5175444-1	ECR-10-008921	26APR10	TS	KB




断面 A-A
(SECT. A-A)

断面 B-B
(SECT. B-B)

- NOTES; Δ MUST BE KEPT BETWEEN $-Z$ AND 2
2 THE MATING PLUG HSG. PART NUMBER; 174515, 175442
3 RECOMMENDED MOUNTING SCREW; 3mm DIA, 6mm LENGTH MAX. >
PAN HEAD, CLASS 2 TAPPING SCREW SPECIFIED IN JIS B1115, B1122
(TIGHTENING TORQUE; 0.4N-m (4Kg-cm) MAX. >
4 APPLICABLE PRODUCT SPEC NO. 108-5280
 Δ CIRCUIT NUMBER
POWER CIRCUIT NO. ① ~ ⑱
SIGNAL CIRCUIT NO. ⑲ ~ ⑳
 Δ INDICATED PREFIX AND ID MARK OF PRODUCT P/N BY HOT MARK

注 記

- Δ $-Z$ 面から2mmの範囲で測定
2. 嵌合相手ハウジング型 174515, 175442
3. 推奨取付ねじ : JIS B1115, B1122 タッピンねじ, なべ2種
呼び径3, 長さ6mm以下 (締付けトルク : 0.4N-m (4Kg-cm) 以下)
4. 適用製品規格番号 : 108-5280
 Δ 回路番号
パワー回路 ① ~ ⑱
シグナル回路 ⑲ ~ ⑳
 Δ 適用製品型番のプリフィックス及びIDマークを
カラーホットマークにて表示



54	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD $\times 8$	-	20, 24, 26~28, 32~34	GRAY	4-5175444-6
53	SELECTIVE-TIN (MATTE)	SELECTIVE-TIN (BRIGHT) $\times 26$	-	-	-	-
		SELECTIVE GOLD $\times 13$	2~5	20~24, 29~32	WHITE	3-5175444-1
		SELECTIVE-TIN (BRIGHT) $\times 21$	-	-	-	-
SEE CUSTOMER DRAWING 9-175444-1						
7	TIN-LEAD	PRE-TIN $\times 26$	14, 17, 18	24~26, 32, 34	GRAY	9-175444-1
6	TIN-LEAD	SELECTIVE GOLD $\times 8$	-	19~22, 27~30	WHITE	7-175444-6
		PRE-TIN $\times 26$	-	-	-	-
5	TIN-LEAD	SELECTIVE GOLD $\times 8$	4, 6, 9, 12	26, 28, 29, 34	LIGHT GRAY	5-175444-9
		PRE-TIN $\times 26$	-	-	-	-
5	TIN-LEAD	SELECTIVE GOLD $\times 4$	5, 6, 11, 12	-	GRAY	5-175444-6
		PRE-TIN $\times 30$	-	-	-	-
5	TIN-LEAD	SELECTIVE GOLD $\times 8$	4, 6, 9, 12	26, 28, 29, 34	BLACK	5-175444-2
		PRE-TIN $\times 26$	-	-	-	-
5	TIN-LEAD	SELECTIVE GOLD $\times 8$	4, 6, 9, 12	26, 28, 29, 34	WHITE	5-175444-1
		PRE-TIN $\times 26$	-	-	-	-
4	TIN-LEAD	SELECTIVE GOLD $\times 8$	-	20, 24, 26~28, 32~34	GRAY	4-175444-6
		PRE-TIN $\times 26$	-	-	-	-
3	TIN-LEAD	SELECTIVE GOLD $\times 13$	2~5	20~24, 29~32	GRAY	3-175444-6
		PRE-TIN $\times 21$	-	-	-	-
3	TIN-LEAD	SELECTIVE GOLD $\times 13$	2~5	20~24, 29~32	BLACK	3-175444-2
		PRE-TIN $\times 21$	-	-	-	-
3	TIN-LEAD	SELECTIVE GOLD $\times 13$	2~5	20~24, 29~32	WHITE	3-175444-1
		PRE-TIN $\times 21$	-	-	-	-
2	TIN-LEAD	SELECTIVE GOLD $\times 16$	-	19~34	WHITE	2-175444-1
		PRE-TIN $\times 18$	-	-	-	-
0		PRE-TIN $\times 34$	-	-	ORANGE	175444-8
0		PRE-TIN $\times 34$	-	-	GRAY	175444-6
0		PRE-TIN $\times 34$	-	-	BLUE	175444-5
8	SELECTIVE-TIN (MATTE)	SELECTIVE-TIN (BRIGHT) $\times 34$	-	-	WHITE	175444-3
0		PRE-TIN $\times 34$	-	-	BLACK	175444-2
0		PRE-TIN $\times 34$	-	-	WHITE	175444-1
Δ MARKING マーキング	SOLDERING SIDE 手付け側	CONTACT SIDE 接触部側	POWER CIRCUIT NO. パワー回路		SIGNAL CIRCUIT NO. シグナル回路	
	CONTACT FINISH コンタクト仕上		GOLD PLATED CIRCUIT NO. 金めっき回路番号		COLOR 色	PART NUMBER 製品型番

THIS DRAWING IS A CONTROLLED DOCUMENT.				Tyco Electronics Corporation Kawasaki, Japan			
DIMENSIONS: 単位: 寸 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		NAME 名称		34POSITION CAP HOUSING ASS'Y 040/070 SERIES HYBRID I/O CONNECTOR	
GENERAL TOLERANCE		FINISH 仕上		WEIGHT		RESTRICTED TO	
0<≦ 10 : ± 0.2 10<≦ 30 : ± 0.25 30<≦ 100 : ± 0.3 ANGLES : $\pm 3^\circ$		SEE TABLE		CUSTOMER DRAWING		SCALE 尺度 2:1	
MATERIAL 材料		HOUSING : PBT CONTACT : BRASS		DRAWING NO 番号		SHEET 1 of 1	
				A2 00779 C=175444		REV P4	