


4

3

2

1

LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
			N1	REVISED PER ECR-10-004379	08MAR10	HMR JR



- 1 FOR 1.27[.050] TO 2.08[.082] WIRE INS DIA
- 2 TONGUE MATERIAL THK 0.46±0.05[.018±.002]
- 3 APPLIES FROM EDGE OF METAL BARREL TO CENTERLINE OF STUD HOLE.

OBSOLETE	100	LOOSE PC, BOX	BODY & SLEEVE: COPPER ASTM-B152 TIN PL ASTM-B545 INSULATION: NYLON COLOR: YELLOW	8-321620-1
	1	WIRE TERMINAL		321620
	QTY	DESCRIPTION	MATERIAL & FINISH	PART NO

321620	1-321620-0
PART NO	PART NO ON TAPE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
SEE TABLE

FINISH
SEE TABLE

DWN
RAGHAVENDRA
08MAR10

CHK
JEFF RUTH
08MAR10

APVD
TOM MICHIELUTTI
08MAR10

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
—

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME
TERMINAL NYLON - PIDG - RING TONGUE
WIRE SIZE: 26-22

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-321620

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
10:1

SHEET
1 OF 1

REV
N1