

Specifications for BMP71 Label Printer Labels

Adhesive	Permanent Acrylic
After Process	Yes, this material will work with this application
Application	Circuit Board & Component Identification
Approval/Compliance	UL Recognised;Meets the requirements of MIL-STD-202G, Notice 12, Method 215K
Article No.	114728
Board Application	SMT - Top/Bottom;Through Hole - Bottom;Through Hole - Top
Brady Material No.	B-457
Material Type	Polyimide
Brand	UltraTemp™ Series
Colour	White
Finish	Gloss
Description	Labels for the BMP™71 Label Printer. Please Note: This material is UL approved with its respective ribbon. See the Recommended Ribbon Series for the appropriate ribbon to use.
Max. Characters per Line	15
Max. Lines of Text	2
Max. Service Temp. °C	300
Order Reference	M71-10-457
Printer Compatibility	BMP71
Ribbon Series	M71-R6000HF
Shape	Rectangle
Size - Height (mm)	6.35
Size - Width (mm)	19.05
Additional Information	Good contrast and smear resistance
Surface Mount Technology SMT	Yes, this material will work with this application
Through Hole	Top: Yes, Bottom: Yes

Technology	
Total Qty per Pack	750 Label(s) / Box
Vertical Repeat (mm)	9.53
Industry	Electronics
Min. Service Temp. °C	-70
QTY. per Row	1
Thickness (mm)	0.111