

Specifications:

Body Orientation	Straight
Body Plating	Nickel
Bulkhead	Yes
Cable Type	RG178
Contact Material	Brass
Contact Plating	Gold
Gender	Female
Impedance	50 Ω
Mounting Type	Panel Mount
Operating Frequency	4 GHz
Polarity	Normal
Termination Method	Clamp
Contact Resistance	1.5 m Ω (Maximum Central), 0.5 m Ω (Maximum Outer)
Insulation Material	PTFE (Internal)
Insulation Resistance	5000 M Ω
Number of Functions	500
Operating Temperature Range	-65 to +85°C
Standards Met	RoHS Compliant
Voltage Rating	750 V (Insulation), 335 V (Working)