



Main

Range of product	Cable ends
Product or component type	Cable end
Cable end size	Medium
Standards	NF C 63-023
Quantity per set	Set of 100
Cable cross section	25 mm ²

Complementary

Cable end type	Single conductor
Additional information	For additional marker tag holder
Colour	Black
Bezel material	Halogen-free plastic
Tube material	Copper conforming to ISO 1337
Number of cables	1
AWG gauge	4
Bezel size	Ø 12 mm
Tube diameter	8.15 mm
Length	30 mm
Tube length	17.5 mm
CAD overall width	12 mm
CAD overall height	14 mm
CAD overall depth	30 mm
Product weight	0.156 kg

Environment

Ambient air temperature for operation	-20...105 °C
---------------------------------------	--------------