






PIN ASSIGNMENT



*	390	CARTON:46*30*25CM	A/R	PCS
*	390	PE BAG:30*28*0.08MM	A/R	PCS
*	390	PE BAG:8*10*0.06MM	1	PCS
13	200034000021	TUBE-HT- $\phi 2.0$ *5MM(薄型)	8	PCS
12	230010000024	CORE:17.5*28.5*9.5MM	2	PCS
11	240010800005	SRW-RE32/BK10	4	PCS
10	120010000031	PVC-BK10/50	66	G
9	230020000002	SOL-WIRE-63/37-1.2	3.0	G
8	210010000038	FOIL-CU-30*60MM	2	PCS
7	210030000132	HI TEAMP TAPE:W:25MM;L:80MM	2	PCS
6	120020000001	PE-5321	13	G
5	230020000001	SOL-WIRE-63/37-1.0	0.6	G
4	200034000050	TUBE-HT- $\phi 1.0$ *15MM(thin)	8	PCS
3	200034000030	TUBE-HT- $\phi 3.0$ *10MM(thin)	8	PCS
2	110361025004	D.V.I-24+KEY-M(BLACK)(Nickel Plated shell)(PIN GOLD FLASH)	2	PCS
1		UL20276-[28*(1P+D+A+MY)*4C+28*1P+28*3C]+A+D+B-BK10- $\phi 7.3$	5.0	M
NO	PART NO.	DESCRIPTION	QTY	UNIT



OUTER MOLDING	AV-DVI053	HT006		
INNER MOLDING	AV-DVI052			
		ITEM: 489365		REV: R.
DRAW,BY: 鍾有涓		SCALE:NONE	DATE: 2007-12-02	
CHECK,BY:		CUSTOMER:C331<RS>	PAGE: 1/1	
APP,BY:		CUSTOMER P/N:		
ALL DIMENSIONS IN mm				