

## Plug-in module - LDP3- 12- 24DC - 2833770

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Plug-in module, for mounting on PR3, with damping diode and yellow LED, polarity: A1+, A2-, input voltage: 12 -24 V DC  $\pm$  20%

### Why buy this product

- Mechanical coding to protect against mismatching
- Attenuation of reverse voltage induced in coil



### Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 933968
Weight per Piece (excluding packing)	6.29 g
Custom tariff number	85366990
Country of origin	China

### Technical data

#### Standards and Regulations

Connection in acc. with standard	CUL
----------------------------------	-----

### Classifications

#### eCl@ss

eCl@ss 4.0	27371190
eCl@ss 4.1	27371190
eCl@ss 5.0	27371692
eCl@ss 5.1	27371692
eCl@ss 6.0	27371603
eCl@ss 7.0	27371603
eCl@ss 8.0	27371010

# Plug-in module - LDP3- 12- 24DC - 2833770

## Classifications

### ETIM

ETIM 2.0	EC001456
ETIM 3.0	EC001456
ETIM 4.0	EC001456
ETIM 5.0	EC000683

### UNSPSC

UNSPSC 6.01	30211917
UNSPSC 7.0901	39121516
UNSPSC 11	39121516
UNSPSC 12.01	39121516
UNSPSC 13.2	39121516

## Approvals

### Approvals

---

#### Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

---

#### Ex Approvals

---

#### Approvals submitted

---

### Approval details

UL Recognized

cUL Recognized

EAC

cULus Recognized

## Plug-in module - LDP3- 12- 24DC - 2833770

### Drawings

Circuit diagram

