

95  
6

## Bowden Cable Cutter



95 61 150

- for Bowden cables and soft wire rope up to 3.0 mm dia. (also V2A)
- smooth and clean cutting due to special shape of the cutting edges
- sickle shape cutting edges surround the material and prevent the wire rope fanning out
- little handforce required due to very high transmission ratio
- with opening spring and locking device
- cutting edges additionally induction hardened

- High-grade special tool steel, forged, oil-hardened



Article No.	EAN 4003773-	↔ mm	Shears	Head	Handles	Cutting capacities Ø mm	⚖ g
95 61 150	065197	150	black atramentized	polished	plastic coated	3	205

95

## Wire Rope and ACSR-Cable Cutters



95 71 600

- for wire ropes and steel rods, copper and aluminium cables
- suitable for cutting overhead cables with strain relief wire (ACSR-cables)
- angular cutting blades allow cutting of single rope wire
- optimum transmission ratio for high cutting performance
- bolted cutter head, replaceable
- low weight
- Cutter head: high-grade special tool steel, oil-hardened
- Handles: aluminium, high-strength



95 77 600

**95 81 600**  
 with reinforced cutter head for higher performance, also cuts piano wire

Article No.	EAN 4003773-	↔ mm	Head	Handles	Cutting capacities				AWG	⚖ g
					mm²	Ø mm	Ø mm	Ø mm		
95 71 445	014522	445	polished	with plastic grips	95	10.0	7.0		3/0	1083
95 71 600	014539	600	polished	with plastic grips	150	14.0	9.0		5/0	1716
95 77 600	025313	600	polished	with dipped insulation	150	14.0	9.0		5/0	2359
95 81 600	025344	600	polished	with plastic grips	150	16.0	10.0	4.5	5/0	2256

95 79 445	025320	Spare cutter head for 95 71 445								
95 79 600	025337	Spare cutter head for 95 71 600 / 95 77 600								
95 89 600	025351	Spare cutter head for 95 81 600								