

DPRO STICK 14 W/825 E27

OSRAM DULUX PRO STICK | Compact fluorescent integrated, stick shape



Areas of application

- High-quality domestic and professional environments
- Wherever light is required quickly
- General illumination
- Outdoor use in enclosed and ventilated luminaires only

Product benefits

- Excellent price/performance ratio
- Extremely fast lumen ramp-up thanks to Quick Light Technology
- Great variety of light colors

Product features

- Quick Light: 60 % light output in ≤ 20 s
- Warm Comfort Light – energy-saving light similar to that of an incandescent lamp
- Good quality of light; color rendering index $R_a: \geq 80$; constant chromaticity



Technical data

Electrical data

Nominal wattage	14.00 W
Nominal voltage	220...240 V
Claimed equiv. conventional lamp power	62 W
Power factor λ	0.55
Nominal current	0.14 A
Operating frequency	50...60 Hz

Photometrical data

Light color	825
Light color as per EN 12464-1	Warm Comfort Light
Color rendering group	1B

Light technical data

Starting time	< 1.0 s
---------------	---------





Temperatures

Ambient temperature range	0...+50 °C
---------------------------	------------

Product datasheet

Additional product data

Light colors, color rendering properties and Light Color Coordinates for OSRAM DULUX® - lamps with integrated control gear

Light Color LUMILUX®	Color Rendering Index (CRI), Ra	Target Color Coordinate X	Target Color Coordinate Y	Color Temperature [K]	
825 Warm Comfort Light	≥ 80	0.485	0.427	2500	
827 Warm White	≥ 80	0.463	0.420	2700	
840 Cool White	≥ 80	0.380	0.380	4000	
865 Cool Daylight	≥ 80	0.313	0.337	6500	

1 | Dateiname | ORG CODE | Initial
Technische Zeichnung | T15W00000



Luminous intensity distribution

Base (standard designation)	E27
Appropriate disposal acc. to WEEE	Yes


Capabilities

Dimmable	No
-----------------	----

Certificates & standards

Cleaning instruction in case of breakage	What to do if a lamp containing mercury breaks?
---	---

Light Distribution



Spectral power distribution

Safety advice

In case of lamp breakage: www.osram.com/brokenlamp
Not for use with external dimmers or electronic switches.

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321987013	DPRO STICK 14 W/825 E27	Shipping carton box 10	240 mm x 156 mm x 103 mm	3.86 dm ³	868.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.