

Adapter plate - HC-B 16-ADP/2 DSUB 50 - 1775541

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




D-SUB adapter plate, for two D-SUB connectors, no. of positions 50, housing series HC-B 16...

The illustration shows version HC-B 16-ADP/2 DSUB 37



Key commercial data

Packing unit	2 pc
Minimum order quantity	2 pc
GTIN	 4 017918 038144
Weight per Piece (excluding packing)	13.0 g
Custom tariff number	85472000
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length	85 mm
Height	34.5 mm
Hole diameter	3.2 mm
Drill hole distance, horizontal	77.5 mm
Drill hole distance, vertical	27 mm

General

Note	For housing HC-B16
Material	PA
Inflammability class according to UL 94	HB
Color	gray
Number of positions	50
Type	B16

Adapter plate - HC-B 16-ADP/2 DSUB 50 - 1775541

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209

ETIM

ETIM 3.0	EC002309
ETIM 4.0	EC002309
ETIM 5.0	EC002309

UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted


Approval details

EAC

Drawings

Adapter plate - HC-B 16-ADP/2 DSUB 50 - 1775541

Dimensioned drawing



See assembly instruction