

# Housing - HC-B 16-TFQ-60/O1M25S - 1604807


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



HEAVYCON sleeve housing B16, for double locking latch, height 60 mm, with support 1x M25, lateral conductor exit



## Key commercial data

Packing unit	10 pc
GTIN	 4 017918 881856
Weight per Piece (excluding packing)	205.73 g
Custom tariff number	85389099
Country of origin	Germany

## Technical data

### Dimensions

Height	60 mm
Width	43 mm
Length	94 mm

### Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

### General

Note	For contact inserts HC-B16, BB32, D40, DD72, HS6, M, K
Type	B16
Housing type	Sleeve housings
Locking type	For double locking latch
No. of cable exits	1
Cable exit	Lateral
Screw connection	none
Type of the screw connection	1x M25
Housing material	Aluminum die-cast

# Housing - HC-B 16-TFQ-60/O1M25S - 1604807

## Technical data

### General

Housing surface material	Powder-coated, gray
Assembly instructions	For half and full screw connections

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

### ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

## Approvals

### Approvals

---

Approvals

GOST

---

Ex Approvals

---

Approvals submitted

---

### Approval details

## Housing - HC-B 16-TFQ-60/O1M25S - 1604807

### Approvals



### Accessories

#### Accessories

#### Full screw connection

Cable gland - HC-K-KV-M25(11-17) - 1690639



Plastic screw connection up to 5 bar, thread length: 8 mm, cable diameter: 11 - 17 mm, WAF 29, screw connection: M25

Cable gland - HC-M-KV-M25(11-16) - 1690574



Metal screw connection up to 5 bar, thread length: 7 mm, cable diameter: 11 - 16 mm, WAF 27, screw connection: M25

Cable gland - HC-M-KV-M25(14-21) - 1646007



Metal screw connection up to 5 bar, thread length: 7 mm, cable diameter: 14 - 21 mm, WAF 34, screw connection: M25

Cable gland - HC-M-KV-M25(1ASI) - 1584020



Metal screw connection for an AS-Interface flat-ribbon conductor, thread type M25

#### Multiple screw connection

## Housing - HC-B 16-TFQ-60/O1M25S - 1604807

### Accessories

Cable gland - HC-M-KV-M25(1X10/1X11) - 1580228



Special cable screw connection M25, brass nickel-plated, grommet with 10 mm and 11 mm holes

---

### Drawings

Dimensioned drawing

